

TIFFEN

TI-C-SL



Tiffen *(see online price list for complete specs)*

CODE	ITEM	W	D	AH	BH	SW	SD	SH	WT
TI-C-AA	Chair	32	37	26	38.5	23	21	19.5	90
TI-C-SL	Chair	32	37	23	38.5	23	21	19.5	90
TI-L-SL	Loveseat	55	37	23	38.5	46	21	19.5	125

W=Width D=Depth AH=Arm Height BH=Back Height SW=Seat Width SD=Seat Depth SH=Seat Height WT=Weight

TIFFEN SPECIFICATIONS signature series 
BACK

The back frame is constructed with 7/8" engineered paneling with the support system constructed of 11-gauge sinuous wire linked together with a 12-gauge tie wire. The back support system is covered with woven versare fabric with one piece of high-density polymeric foam. The outside back of the frame is covered with woven tyvar and an additional piece of high-density polymeric foam. The back frame is secured to the base frame with patented metal brackets attached to the base frame with metal-to-metal connections.

BASE

The base frame is constructed completely of 7/8" engineered paneling. Patented metal brackets are attached to the base frame with 5/16" -18 x 1" button-head cap screws into steel receivers (t-nuts) creating a metal-to-metal connection. Legs are attached with steel bolts and feet have plastic or metal glides.

SEAT

Seat cushions are of high-density, polymeric foam. The top and bottom is covered with a laminated, polyurethane, moisture-barrier membrane. The cushion is secured to the base frame by a nylon security strap (steel cable optional).

ARM

Arm frames are constructed completely of 7/8" engineered paneling and 80-point chipboard. The arm frames are covered with polymeric high-density urethane foam. The arm frame is attached to the base frame by sliding machined slots onto patented metal brackets on the base frame.

UPHOLSTERY

All upholstery offerings conform to California Technical Bulletin 117 fire code standard. All estimated yardage quotes are based on 54" non-matched, solid color material unless otherwise specified. Additional yardage and matching fees may apply.

ASSEMBLY AND DISASSEMBLY

No tools are needed. All components can be disassembled and removed by loosening the thumbscrew and sliding the components out of the tamper-proof interlocking state. Assembly can be completed within minutes without the usage of tools, and all upholstery fastens with hook and loop tape, facilitating removal and replacement of covers.

WARRANTY

This product is warranted against defects in materials and workmanship and against structural damage occurred through normal use for 35-years from date of purchase. Foam is also covered under the 35-year period while fabric is generally covered under the fabric company's warranty. Transformations does not warrant any materials beyond its control.

ADDITIONAL OPTIONS

CAL 133 fabric treatment may be applied for an additional fee per yard.

This is an abbreviated specifications list. For complete specs, contact Customer Service.

AVAILABLE OPTIONS:

Chair (2 Arm Styles)
Loveseat in all styles

UPGRADE OPTIONS:

CAL133



SEE PRICE LIST

FOR MORE INFORMATION

FOOT OPTIONS:


TF10

STAIN CHOICES:

Visit our OPTIONS web page
for samples:

www.transformationsfurniture.com/options



TI-L-SL
Loveseat



TI-C-SL
chair-sloped arm



TI-C-AA
chair-arched arm



For More Information:

Transformations Furniture 310 Racquet Drive Fort Wayne IN 46825

www.trfurniture.com customerservice@trfurniture.com phone: **800.440.9337**